

PRO225LM

Precise, Reliable & Adaptable

The PRO225LM provides an optimal balance of positioning performance, payload capacity and size. Compared to the narrower PRO190LM, PRO225LM is capable of carrying considerably higher payloads due to its larger bearings and motor. Combining superior craftsmanship and the highest quality components, PRO225LM stages consistently and reliably deliver best-in-class positioning performance.

Key Applications

PRO225LM mechanical bearing, direct-drive linear stages are extremely versatile, trusted and proven in medium- and high-performance applications, such as:

- Laser material processing
- Precision metrology, inspection & microscopy
- ◆ Electronics & circuit board manufacturing & inspection
- Display processing
- Synchrotron & light source experiments
- Medical device manufacturing
- Semiconductor fabrication
- Fiber optics & silicon photonics processing
- Additive manufacturing & precision assembly

KEY FEATURES:

- Provides SUBSTANTIAL PAYLOAD-CARRYING CAPACITY
- Ironless, cogless linear motor delivers SMOOTH,
 ULTRA-PRECISE MOTION
- EXCELLENT POSITIONING & DYNAMIC
 CAPABILITIES in a cost-effective package
- ◆ BEST-IN-CLASS GEOMETRIC PERFORMANCE ensures superior workpoint accuracy
- Rugged, reliable construction is ideal for VERSATILE INDUSTRIAL USE
- Hardcover & side seals offer PROTECTION
 AGAINST CONTAMINATION & PARTICULATES
- ThermoComp® option automatically COMPENSATES FOR THERMAL DISTURBANCES
- VACUUM- & CLEANROOM-COMPATIBLE versions available

PRO225LM SPECIFICATIONS

Mechanical Specifications			PR0225LM				
Travel		100	200	300	400		
Accuracy ⁽¹⁾	Standard	±4 μm	±8 μm	±10 μm	±12 μm		
	Calibrated	±1 μm	±1 μm	±1 μm	±1 μm		
Resolution (Min. Incremental Motion)			5 nm (-E1 Encoder)				
Bidirectional Repeatability ⁽¹⁾		±0.3 μm	±0.4 μm	±0.4 μm	±0.4 μm		
Horizontal Straightness ⁽¹⁾		±1.5 µm	±2.5 μm	±3.5 μm	±4.5 μm		
Vertical Straightness ⁽¹⁾		±1.5 µm	±2.5 μm	±3.5 μm	±4.5 μm		
Pitch		25 µrad	39 μrad	50 μrad	60 μrad		
Roll		27 μrad	39 µrad	50 μrad	60 μrad		
Yaw		27 μrad	39 μrad	50 μrad	60 μrad		
Maximum Speed ⁽²⁾			2 m/s				
Maximum Acceleration ⁽²⁾			3 g				
Maximum Force, Continuous			153 N – Standard 251.6 N – With Air Cooling (20 psig)				
Load Capacity ⁽³⁾	Horizontal		100 kg				
	Side		100 kg				
Moving Mass			8.4 kg				
Stage Mass		23.8 kg	26.9 kg	30.1 kg	33.3 kg		
Material			Anodized Aluminum				
MTBF (Mean Time Between Failure)			20,000 Hours				

Notes:

- 1. Certified with -PL1/-PL2 option.
- 2. Requires the selection of an appropriate amplifier with sufficient voltage and current.
- 3. Axis-orientation for on-axis loading is listed.
- 4. Specifications are for single-axis systems measured 25 mm above the tabletop. Performance of multi-axis systems is payload and workpoint dependent. Contact factory for multi-axis applications.



PRO225LM SPECIFICATIONS

Mechanical Specifications			PR0225LM				
Travel		500	600	800	1000		
Accuracy ⁽¹⁾	Standard	±14 μm	±15.5 μm	±17 μm	±18 μm		
	Calibrated	±1 μm	±1 μm	±1.5 μm	±1.5 μm		
Resolution (Min. Incremental Motion) ⁽²⁾			5 nm (-E1 Encoder)				
Bidirectional Repeatability ⁽¹⁾		±0.4 μm	±0.4 μm	±0.5 μm	±0.5 μm		
Straightness ⁽¹⁾		±5.5 μm	±6.5 μm	±8 μm	±9.5 μm		
Flatness ⁽¹⁾		±5.5 μm	±6.5 μm	±8 μm	±9.5 μm		
Pitch		70 µrad	80 μrad	90 µrad	110 µrad		
Roll		70 µrad	80 μrad	90 µrad	110 µrad		
Yaw		70 µrad	80 µrad	90 μrad	110 µrad		
Maximum Speed ⁽³⁾		2 m/s					
Maximum Acceleration(3)			3 g				
Maximum Force, Continuous		153 N – Standard 251.6 N – With Air Cooling (20 psig)					
Load	Horizontal	100 kg					
Capacity ⁽⁴⁾	Side	100 kg					
Moving Mass		8.4 kg					
Stage Mass		36.5 kg	39.7 kg	46.1 kg	52.5 kg		
Material		Anodized Aluminum					
MTBF (Mean Time Between Failure)		20,000 Hours					

Notes:

- 1. Certified with -PL1/-PL2 option.
- 2. Requires the selection of an appropriate amplifier with sufficient voltage and current.
- 3. Axis-orientation for on-axis loading is listed.
- 4. Specifications are for single-axis systems measured 25 mm above the tabletop. Performance of multi-axis systems is payload and workpoint dependent. Contact factory for multi-axis applications.

Electrical Specifications		
Drive System	Brushless Linear Servomotor	
Feedback	Non-contact Linear Encoder -E1: 1 Vpp, 20 μm signal period -E2: Digital RS422, 0.1 μm electrical resolution	
Maximum Bus Voltage	340 VDC	
Limit Switches	5 V, Normally-Closed	
Home Switch	Near Center	



PR0225LM ORDERING OPTIONS

Travel (Required)

-0100	100 mm travel stage
-0200	200 mm travel stage
-0300	300 mm travel stage
-0400	400 mm travel stage
-0500	500 mm travel stage
-0600	600 mm travel stage
-0800	800 mm travel stage
-1000	1000 mm travel stage

Other travel options are available upon request. Contact Aerotech for more information.

Tabletop (Required)

-TT1 Tabletop with metric dimension mounting

NOTE: -TT1 option required for lower axis of XY.

Other tabletop options are available upon request. Contact Aerotech for more information.

Feedback (Required)

- **-E1** Incremental linear encoder, 1 Vpp
- -E2 Incremental linear encoder, 0.1 μm digital TTL output

Other feedback options are available upon request. Contact Aerotech for more information.

Cable Management (Required)

- -CMSO No external CMS, motor/feedback connector bracket on carriage
- -CMS1 External CMS for single axis
- -CMS2 External CMS for lower-axis of two-axis PRO (XY) assembly
- -CMS3 External CMS for lower-axis of two-axis (XZ or XT) assembly
- -CMS4 External CMS for upper-axis of two-axis PRO (XY) assembly
- -CMS5 External CMS for upper-axis of two-axis (YZ or YT) assembly
- -CMS6 External CMS for lower-axis of three-axis (XYZ or XYT) assembly
- -CMS7 External CMS for lower-axis of three-axis (XZT) assembly
- -CMS8 External CMS for upper-axis of four-axis (XYZT) assembly
- -CMS9 External CMS for lower-axis of four-axis (XYZT) assembly

Lifting Hardware (Optional)

-LF Lifting hardware

NOTE: Lifting option only available on travels 300 mm and greater. Lifting should never be ordered on the upper-axis of an XY set (only order on lower-axis).

ThermoComp (Optional)

-TCMP ThermoComp integrated thermal compensation, single or lower axis



PRO225LM ORDERING OPTIONS

Metrology (Required)

- **-PL0** No metrology performance plots
- **-PL1** Metrology, uncalibrated with performance plots
- -PL2 Metrology, calibrated (HALAR) with performance plots

Integration (Required)

Aerotech offers both standard and custom integration services to help you get your system fully operational as quickly as possible. The following standard integration options are available for this system. Please consult Aerotech if you are unsure what level of integration is required or if you desire custom integration support with your system.

-TAS Integration - Test as system

Testing, integration and documentation of a group of components as a complete system that will be used together (ex: drive, controller and stage). This includes parameter file generation, system tuning and documentation of the system configuration.

-TAC Integration - Test as components


Testing and integration of individual items as discrete components. This is typically used for spare parts, replacement parts or items that will not be used or shipped together (ex: stage only). These components may or may not be part of a larger system.


Accessories (To Be Ordered As Separate Line Item)

ALIGN-NPA	Non-precision XY assembly
ALIGN-NPAZ	Non-precision XZ or YZ assembly
ALIGN-PA10	XY assembly; 10 arc sec orthogonality. Alignment to within 7 microns orthogonality
	for short travel stages.
ALIGN-PA10Z	XZ or YZ assembly with L-bracket; 10 arc second orthogonality. Alignment to
	within 10 microns orthogonality for short travel stages.
ALIGN-PA5	XY assembly; 5 arc sec orthogonality. Alignment to within 3 microns orthogonality
	for short travel stages.
ALIGN-PA5Z	XZ or YZ assembly with L-bracket; 5 arc second orthogonality. Alignment to within 5
	microns orthogonality for short travel stages.



PR0225LM SPECIFICATIONS







Measurement data showing successful compensation of thermal related positioning errors at several temperatures using the ThermoComp feature. Results are typical of stage performance with and without ThermoComp.




PRO225LM DIMENSIONS




PRO225LM SERIES CABLE MANAGEMENT (-CMS0) DIMENSIONS





PRO225LM/PRO280LM/PRO560LM -CMS0



DIMENSIONS: MILLIMETERS

